

[See all 12 Products in Family](#)

TECHSPEC® Elliptical Mirror, 12.7mm Minor Axis, 750 - 1100nm



Stock #72-951 **12 In Stock**

- 1 + MRP ₹11,199

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹11,199 each
Qty 6+	₹8,980 each
Need More?	Request Quote

Product Downloads

General

Flat Mirror **Type:**

Flatness specification is Peak to Valley **Note:**

Physical & Mechanical Properties

±0.020 **Thickness Tolerance (inches):**

Thickness (mm):

3.81 ±0.51

Clear Aperture CA (mm):
11.43 (Minor Axis) 16.15 (Major Axis)

Dimensional Tolerance (inches):
±0.015

Dimensional Tolerance (mm):
±0.38

Major Axis (mm):
17.96

Minor Axis (mm):
12.70

Optical Properties

Coating Type:
Dielectric

Coating:
Dielectric Mirror (750-1100nm)

Surface Flatness (P-V):
λ/8

Wavelength Range (nm):
750 - 1100

Substrate:
BOROFLOAT®

Coating Specification:
R_{avg} >98% @ 750 - 1100nm (0 - 45°)
R_{avg} >99% @ 750 - 1100nm (0°)

Surface Quality:
60-40

Damage Threshold, By Design:
1 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Circular Profile When Oriented at 45°
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Enhanced Reflectivity and LIDT over Metallic Coatings

TECHSPEC® Broadband Dielectric Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. TECHSPEC® Broadband Dielectric Elliptical Flat Mirrors feature a BOROFLOAT® substrate and are available with minor axes up to 76.20mm and major axes up to 107.77mm