

[See all 7 Products in Family](#)

E Series 8mm 2/3" Format Fixed Focal Length Lens



Stock #29-995 NEW [CONTACT US](#)

-

1

+

MRP ₹23,099

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹23,099 each
Need More?	Request Quote

Product Downloads

General	
E Series	Product Family:
Note: It is recommended to use C-Mount Camera Imaging Filters when filters are required.	
Fixed Focal Length Lens	Imaging Lens Type:

Physical & Mechanical Properties	
Variable	Iris Option:
40.31	Length (mm):
30.5	Maximum Diameter (mm):
30.5	Outer Diameter (mm):
0.00	Maximum Rear Protrusion (mm):
40.58	Maximum Length (mm):
Optical Properties	
59.1°	Horizontal Field of View @ Max Sensor Format:
49.1°	Horizontal Field of View, 1/1.8" Sensor:
44.0°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
0.003	Numerical Aperture NA, Object Side:
8 (7)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
8.00	Focal Length FL (mm):
250 - ∞	Working Distance (mm):
f/4 - f/16	Aperture (f/#):
0.747	Back Focal Length BFL (mm):
λ/4 MgF ₂	Coating:
14.03	Entrance Pupil Position (mm):
19.28	Object Space Principal Plane (mm):
9.25	Image Space Principal Plane (mm):
2.88	Maximum Distortion (%):
-5.40	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:
VIS	Wavelength:
Sensor	
2/3"	Optimized Sensor Format:
2/3"	Maximum Sensor Format:
2.74	Pixel Size (μm):
Threading & Mounting	
N/A	Filter Thread:
M28.0 x 0.5 (Male)	Front Thread:
C-Mount	Mount:
Environmental & Durability Factors	
-20 to +60	Storage Temperature (°C):
	For questions regarding operating temperature please contact our support team

Regulatory Compliance

Certificate of Conformance:	
View	
Country of Origin:	
China	
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Cost Effective Solution for Systems that Require Large Depth of Field
- Up to 2/3", C-Mount Lens
- Ideal for Logistics and Barcode Scanning Applications

Edmund Optics E Series Fixed Focal Length Lenses provide an affordable fixed focal length imaging solution without compromising performance. These lenses are designed for logistics applications that need to identify product size and shape, read barcodes, and help find product locations. These systems often don't require lenses designed with more demanding specifications like large format sensor coverage and small pixels, which can be costly. Edmund Optics E Series Fixed Focal Length Lenses are a balance of performance and cost designed with a maximum format of 2/3". To maintain affordability in prototyping and mass production, the lens housings have been simplified by removing focusing mechanics. However, the focus can still be adjusted by threading the lenses into and out of the camera, then locked with a locking ring. These lenses maintain performance control with an adjustable iris ranging from f/4 to f/16.