

TECHSPEC® Elliptical Mirror 22.23mm Minor Axis Enhanced Aluminum



Stock **#32-131** 10 TO 12 DAYS

- 1 + **₹8,091.00**

ADD TO CART

Qty 1-5
₹8,091.00
Qty 6+
₹6,482.00
Volume Pricing
Request Quote

Get Product Downloads



Minor Axis (mm):
22.23

Major Axis (mm):
31.42

Surface Flatness (P-V):
λ/8

Substrate:

BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 20.02 (Minor Axis) 28.27 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 6.35
Thickness Tolerance (inches): ±0.030
Thickness Tolerance (mm): ±0.76
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant