

TECHSPEC[®] Elliptical Mirror 38.1mm Minor Axis UV Enhanced Aluminum



Stock **#43-577** 1 In Stock

-

1

+

₹11,444

ADD TO CART

Volume Pricing	
Qty 1-5	₹11,444 each
Qty 6-25	₹9,147 each
Qty 26-49	₹8,602 each
Need More?	Request Quote

Product Downloads

General	
Flatness specification is Peak to Valley	Note:
Flat Mirror	Type:

Physical & Mechanical Properties	
38.10	Minor Axis (mm):

53.87	Major Axis (mm):
±0.38	Dimensional Tolerance (mm):
±0.015	Dimensional Tolerance (inches):
34.29 (Minor Axis) 48.49 (Major Axis)	Clear Aperture CA (mm):
9.53 ±0.76	Thickness (mm):
±0.030	Thickness Tolerance (inches):

Optical Properties

λ/8	Surface Flatness (P-V):
BOROFLOAT®	Substrate: ☐
60-40	Surface Quality:
R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm	Coating Specification:
Enhanced Aluminum (250-700nm)	Coating:
Metal	Coating Type:
0.25 - 0.7	Wavelength Range (μm):
250 - 700	Wavelength Range (nm):
0.5 J/cm ² @ 355nm, 10ns	Damage Threshold, Reference: ☐

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

See Figure A in Technical Information tab for dimensional diagram.

- Circular Profile When Oriented at 45°
- Ideal for Redirecting Light
- Multiple Sizes and Coatings Offered

TECHSPEC® λ/8 Precision Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors have a circular profile when they are oriented at 45°. TECHSPEC® λ/8 Precision Elliptical Flat Mirrors feature a BOROFLOAT® substrate. Multiple sizes and coating options are offered to best suit a wide range of applications.

Technical Information

Fig.	Minor Axis (mm)	Major Axis (mm)	Thickness (mm)	Stock No.					
				Uncoated	Protected Aluminum	UV Enhanced Aluminum	Enhanced Aluminum	Protected Gold	Protected Silver
B	12.70	17.96	3.81	#32-270	#32-271	#43-573	#32-272	#32-273	#89-454
B	22.23	31.42	6.35	#32-093	#30-836	#43-574	#32-131	#32-085	#89-455
B	26.97	38.15	6.35	#32-094	#30-837	#43-575	#32-132	#32-086	#89-456
A	31.75	44.91	9.53	#32-095	#30-205	#43-576	#32-133	#32-087	#89-457
A	38.10	53.87	9.53	#32-096	#30-258	#43-577	#32-134	#32-088	#89-458
A	47.63	67.36	11.68	#32-097	#30-840	#43-578	#32-135	#32-089	#89-459

