

TECHSPEC[®] Elliptical Mirror 38.1mm Minor Axis UV Enhanced Aluminum



Stock #43-577 10 TO 12 DAYS

-

1

+

₹12,180.00

ADD TO CART

Qty 1-5
₹12,180.00
Qty 6+
₹9,744.00
Volume Pricing
Request Quote

Get Product Downloads



Minor Axis (mm):
38.10

Major Axis (mm):
53.87

Surface Flatness (P-V):
λ/8

Substrate:

BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R _{avg} >89% @ 250 - 450nm R _{avg} >85% @ 250 - 700nm
Coating: Enhanced Aluminum (250-700nm)
Coating Type: Metal
Clear Aperture CA (mm): 34.29 (Minor Axis) 48.49 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 9.53
Thickness Tolerance (inches): ±0.030
Thickness Tolerance (mm): ±0.76
Type: Flat Mirror
Wavelength Range (µm): 0.25 - 0.7
Wavelength Range (nm): 250 - 700
Damage Threshold, Reference:  0.5 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant