

**TECHSPEC® Elliptical Mirror 57.15mm Minor Axis Protected Silver**



Stock #89-460 **2 In Stock**

- 1 + MRP ₹41,466

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹41,466 each
Qty 6-25	₹33,193 each
Qty 26-49	₹31,074 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Flat Mirror **Type:**  
  
Flatness specification is Peak to Valley **Note:**

**Physical & Mechanical Properties**

**Thickness Tolerance (inches):**  
±0.060

15.88 ±1.52	<b>Thickness (mm):</b>
51.44 (Minor Axis) 72.75 (Major Axis)	<b>Clear Aperture CA (mm):</b>
±0.031	<b>Dimensional Tolerance (inches):</b>
±0.79	<b>Dimensional Tolerance (mm):</b>
80.82	<b>Major Axis (mm):</b>
57.15	<b>Minor Axis (mm):</b>

## Optical Properties

0.45 - 10	<b>Wavelength Range (µm):</b>
Metal	<b>Coating Type:</b>
Protected Silver (450-10000nm)	<b>Coating:</b>
λ/8	<b>Surface Flatness (P-V):</b>
450 - 10000	<b>Wavelength Range (nm):</b>
<a href="#">BOROFLOAT®</a>	<b>Substrate:</b> <input type="checkbox"/>
R <sub>avg</sub> >98% @450 - 800nm R <sub>avg</sub> >98.5% @2000 - 10,000nm	<b>Coating Specification:</b>
60-40	<b>Surface Quality:</b>
0.5 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details


See Figure B in Technical Information tab for dimensional diagram.

- Circular Profile When Oriented at 45°
- Ideal for Redirecting Light
- Multiple Sizes and Coatings Offered

TECHSPEC® λ/8 Precision Elliptical Flat Mirrors are ideal for research and astronomical applications. Because of their elongated major axis, they are suited to bending and folding light at precise angles with minimum wavefront distortion. These mirrors have a circular profile when they are oriented at 45°. TECHSPEC® λ/8 Precision Elliptical Flat Mirrors feature a BOROFLOAT® substrate. Multiple sizes and coating options are offered to best suit a wide range of applications.

## Technical Information

Fig.	Minor Axis (mm)	Major Axis (mm)	Thickness (mm)	Stock No.					
				Uncoated	Protected Aluminum	UV Enhanced Aluminum	Enhanced Aluminum	Protected Gold	Protected Silver
B	12.70	17.96	3.81	#32-270	#32-271	#43-573	#32-272	#32-273	#89-454
B	22.23	31.42	6.35	#32-093	#30-836	#43-574	#32-131	#32-085	#89-455
B	26.97	38.15	6.35	#32-094	#30-837	#43-575	#32-132	#32-086	#89-456
A	31.75	44.91	9.53	#32-095	#30-205	#43-576	#32-133	#32-087	#89-457
A	38.10	53.87	9.53	#32-096	#30-258	#43-577	#32-134	#32-088	#89-458
A	47.63	67.36	11.68	#32-097	#30-840	#43-578	#32-135	#32-089	#89-459
B	57.15	80.82	15.88	#32-098	#41-131	#43-579	#32-136	#32-090	#89-460
B	66.68	94.28	15.88	#32-099	#42-583	#43-580	#32-137	#32-091	#89-461
B	76.20	107.77	19.05	#32-100	#42-584	#43-581	#32-138	#32-092	#89-462



## Coating Curves