

TECHSPEC[®] f/4, 6mm Focal Length Green Series M12 Lens



6mm Focal Length

Stock **#69-256** **9 In Stock**

-

1

+

₹5,055

ADD TO CART

Volume Pricing	
Qty 1+	₹5,055 each
Need More?	Request Quote

Product Downloads

General	
Green Series	Series:
M12 Imaging Lens	Type:
No	IR Cut Filter:
Standard Lens	Imaging Lens Type:

Physical & Mechanical Properties

Fixed	Iris Option:
11.70	Length (mm):
14	Maximum Diameter (mm):
14	Outer Diameter (mm):
3	Weight (g):

Optical Properties

Horizontal Field of View @ Max Sensor Format: 130.9mm - 46.5°	
Field of View at Max Sensor Format: Horizontal: 129.8mm - 46° Vertical: 95.2mm - 34.6° Diagonal: 168.5mm - 57.7°	
Horizontal Field of View, 1/3" Sensor: 129.8mm - 46.2°	
Horizontal Field of View, 1/4" Sensor: 95.1mm - 34.7°	
80 lp/mm @ 20% Contrast	Resolution:
6.00	Maximum Image Circle (mm):
0.0047	Numerical Aperture NA, Object Side:
5(5)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
6.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/4	Aperture (f/#):
-8.27 @ Full Field	Distortion (%):
4.0 - 3.9	Back Focal Length BFL (mm):
M4 MgF ₂ @ 580nm	Coating Specification:
3.99	Entrance Pupil Position (mm):
6.38	Object Space Principal Plane (mm):
-1.43	Image Space Principal Plane (mm):
-8.27	Maximum Distortion (%):
-5.43	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor

1/3"	Maximum Sensor Format:
8.30	Pixel Size (μm):

Threading & Mounting

N/A	Filter Thread:
M12 x0.5	Mounting Threads:
S-Mount (M12 x0.5)	Mount:

Regulatory Compliance

Compliant	RoHS 2015:
-----------	------------

View		Certificate of Conformance:
Compliant		REACH 241:
China		Country of Origin:
Edmund Optics India Private Limited		Imported By:

Product Details

- Up to 1/2", S-Mbunt Lens
- Up to 0.4 MegaPixels, 8.3µm Pixel Size Sensors
- Board Camera Lens Optimized for Close WD and Finite Conjugate
- 6mm to 25mm Focal Lengths


TECHSPEC® Green Series M12 Lenses designed for use in compact and board level cameras provide excellent image quality in a small, versatile package. Optimized to cover 1/3" and 1/2" sensor formats and weighing only a few grams, these machine vision lenses meet the most demanding space and weight restrictions. Each lens is threaded for M12 x0.5, except the 25.0mm focal length option ([#54-855](#)). TECHSPEC® Green Series M12 Lenses are ideal for wide angle and close focus applications, large area inspect for the automotive, forensic, pharmaceutical, and food industries. Prescription data is available by submitting a [Request for Prescription Form](#).

Note: Compatible [TECHSPEC M12 Imaging Lens Accessories](#) available.


Edmund Optics has created multiple product families of our TECHSPEC® M12 S-Mount Lenses, which are designed to provide high resolution. These high performance lenses feature precision glass designs in a metal housing and have optimized specifications between each product family to meet your application needs.

- **Blue Series M12 Lenses:** High resolution finite conjugate designs optimized for machine vision working distances.
- **Rugged Blue Series M12 Lenses:** [Stabilized ruggedization](#) versions of our Blue Series M12 Lenses, utilizing the same optics.
- Green Series M12 Lenses: Finite conjugate designs optimized for machine vision working distances.
- **Red Series M12 Lenses:** Infinite conjugate designs optimized for high resolution performance out to infinity.
- **HEO Series M12 Lenses:** Harsh Environment Optics (HEO) sealed versions of our Red Series M12 Lenses.
- **Liquid Lens M12 Lenses:** Integrated liquid lens for fast electronic focus.


Technical Information




#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Distortion Plot




#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Relative Illumination Plot




#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Working Distance versus Field of View Plot




#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Modulated Transfer Function (MTF) Plot, 150mm Working Distance, f4



#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Depth of Field Plot, 150mm Working Distance, f4




#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Modulated Transfer Function (MTF) Plot, 250mm Working Distance, f4



#69-256, f/4, 6mm Focal Length Green Series M12 Lens, Depth of Field Plot, 250mm Working Distance, f4

Focal Length	A	B	C**	D	Mounting Thread
6.00	14.0	11.70	4.0 - 3.9	3.5	M12 x0.5
8.00	14.0	20.40	8.9 - 8.7	6.0	M12 x0.5
12.00	16.0	19.50	7.1 - 6.75	6.0	M12 x0.5
25.00	18.0	24.40	12.6 - 11.9	9.0	M16 x0.5



**Minor adjustment required to match WD limits.

