

Fiber Optic Taper For 25mm to 2/3" Sensor



Stock **#55-141** 1 In Stock

-

1

+

MRP ₹2,07,610

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,07,610 each
Need More?	Request Quote

Product Downloads

General	
70 / 30	Core/ Clad Ratio:
Physical & Mechanical Properties	
±0.5, Large End	Diameter Tolerance (mm):
25.00	Height (mm):
27.00	Diameter of Large End (mm):

25:2/3" CCD	Size Ratio:
8.8 x 6.6	Size of Small End (mm):
±0.1	Thickness Tolerance (mm):
±0.1	Dimensional Tolerance (mm):
Optical Properties	
3.00	Distortion (%):
Schott 24 Glass with EMA	Substrate: □
1.00	Numerical Aperture NA:
102 lp/mm	Resolution:
30-20	Surface Quality:
6.00	Resolving Power (µm):
Material Properties	
6.8	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
Environmental & Durability Factors	
-10 to +300	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Coherent Arrangement of Fibers
- Made with EMA Fibers to Absorb Light
- Round-to-Round or Round-to-Rectangular Tapers Types Available

Fiber Optic Tapers utilize a coherent fiber optic plate that transmits either a magnified or reduced image from its input surface to its output surface. These low distortion tapers are made with EMA Fibers to absorb light and are optimized for 1/2" or 2/3" sensor chip sizes. Magnification is a ratio of the diameters of the large and small ends of the tapers. Typical applications include image magnification or reduction, sensor coupling, fluoroscopy, and light sensors.

Fiber Optic Faceplates transmit images from input surface to output surface using coherent fibers. Common uses include CRT/LCD displays, sensor coupling, X-ray imaging and image intensification. All tapers and faceplates are suitable for visible and NIR applications and feature beveled edges.