

TECHSPEC[®] Filter Adapter M62 x 0.75 from M48 x 0.5 (Female)



M62 x0.75 Filter Adapter for 12mm Lens, #34-236



Stock **#34-236** 20+ In Stock

-

1

+

₹3,038

ADD TO CART

Volume Pricing	
Qty 1+	₹3,038 each
Need More?	Request Quote

Product Downloads

General	
Lens Accessory	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
Threading & Mounting	
	Filter Thread:


M62 x0.75 (Female)	
	Front Thread:
M48 x0.5 (Female)	

Regulatory Compliance	
Certificate of Conformance:	
View	
Country of Origin:	
China	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- 1.1", C-Mount Lens
 - Up to 20 MegaPixels, 1.85µm Pixel Size Sensors
 - High Performance (HP), C-Mount Lens for Machine Vision
 - 6.5mm to 50mm Focal Length
- TECHSPEC® HP Series Fixed Focal Length Lenses are designed for the harsh demands of [factory automation \(FA\)](#) and machine vision (MV) applications. The 6.5mm, 8mm, 12mm, 16mm, 25mm, and 35mm lenses are compatible with 1" and 1.1" sensor formats, while the 50mm lens is compatible with up to 4/3" sensor formats. The f/1.8 and f/2.8 apertures provide increased light throughput and high resolution performance. TECHSPEC® HP Series Fixed Focal Length Lenses are C-Mount and feature a locking focus and iris rings to prevent unwanted adjustments, as well as a front filter thread for integrating standard optical filters. Call for OEM Quantity Pricing.
- Edmund Optics has created a family of high performance optical designs (the HP Series family) and developed three customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the HP Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:
- HP Series: Features locking cam focus and iris adjustment. This is the most adjustable version of these optical designs and is the typical high quality machine vision lens.
 - [HPi Series](#): Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
 - [HPr Series](#): All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.

Technical Information



Dimensions					
	Focal Length (mm)	A (mm)	B (mm)	C (mm)	Filter Thread
	8mm, 1.1" Format	70.4	83.5	43.5	M105 x 1 with required adapter #83
	12mm, 1.1 " Format	48	70.1	43.5	M62 x0.75 with required adapter #236
	16mm, 1" Format	48	60.4	57.3 - 59.5	M46 x0.75
	25mm, 1" Format	37.5	45.3	45.3	M34 x0.5
	35mm, 1.1" Format	48.1	65.8	60 - 66	M37 x0.75
	50mm, 4/3" Format	50	72.6	60.5 - 72.6	M37.5 x0.5