


Filter Blocking Wavelengths Below 1290nm in Magnetic, Stackable Holder



#24-211 WnCamD-LCMBeam Profiler

Stock **#71-557** **1 In Stock**

MRP ₹95,049

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹95,049 each
Need More?	Request Quote

Product Downloads

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038

Product Details

- Designed for Use from 355 to 1600nm
- Compatible with Beam Diameters Down to 52 μ m
- Robust and Easy to Use Free Software [Provided](#)
- Measure Beam Wander, M_F, Divergence, and More

DataRay Camera Beam Profilers provide excellent solutions for beam analysis of both continuous wave and pulsed laser sources. Each beam profiler features an integrated CMOS sensor (IR profilers feature Microbolometer sensors) that eliminates comet trailing for higher resolution output and allows for update rates of 60+ Hz. Sensors are available with active sizes of 6.6, 11.3, and 25mm horizontals, enabling measurement of large beam diameters. DataRay Camera Beam Profilers have the added advantage of a free, robust software with analysis features such as M_F measurement, beam wander and logging, and instrument alignment. These profilers are USB3.0/2.0 powered and include a 3m flexible screw locking cable. Neutral density filters with optical densities of 1.0, 2.0, and 4.0 are included.
