

[See all 5 Products in Family](#)

Coherent® Lasercam™ 1098403 | Fixed Attenuator Module

See More by [Coherent®](#)



Stock #59-202 1 In Stock

-

1

+

₹1,01,700

ADD TO CART

Volume Pricing	
Qty 1+	₹1,01,700 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
19	Active Area Diameter (mm):
Optical Properties	
50000	Maximum Incident Energy Density (mJ/cm²):
380 - 2200	Wavelength Range (nm):
50:1 to 10:1	Min. to Max. Attenuation:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details

[#59-202](#) provides a nominal attenuation of 20:1 for randomly polarized light and is rated for up to 20W/cm² or 2J/cm² at 632.8nm.

- 12 and 14-bit Digital USB 2.0 Interface Options
- High Sensitivity and Dynamic Range
- Intuitive BeamView™ Software Included

The Coherent® Lasercam™ Beam Profiler features excellent signal-to-noise ratio and linear response for accurate pulsed as well as CW laser beam dimension and uniformity measurements. The new BeamView™ 4.4 interface software features TCP/IP control and NI LabVIEW™ library suite, enabling efficient and smooth integration of beam profiling into any application. Examples of analysis functions that can be performed on the acquired beam images include: beam centroid location, beam peak intensity position, pointing stability, total relative power/energy in beam, peak power/energy density of beam, beam divergence, ellipticity, beam intensity uniformity, Gaussian fit, beam diameter/width based on second moments or user selectable percentage of peak/total energy.

Technical Information



Intuitive Software Interface

