

[See all 10 Products in Family](#)

Green, Ethernet High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Stock **#21-359** **1 In Stock**

-

1

+

₹50,400

ADD TO CART

Volume Pricing	
Qty 1+	₹50,400 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
SL162-530C1	Model Number:
50,000	LED Lifetime (hours):
1	Number of LEDs:
LED Illuminator	Type of Illumination:

Note: Required Controller #18-645 ; Required Power Supply #66-855	
Manufacturer: Advanced Illumination	
Geometry: Spot Light	
Illumination Mode: Constant, Pulsed, Gated	

Physical & Mechanical Properties

Weight (g): 85.1	
----------------------------	--

Optical Properties

Color: Green	
Wavelength (nm): 530	

Hardware & Interface Connectivity

Connector: C1	
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	

Length of Cable (m): 2	
----------------------------------	--

Environmental & Durability Factors

Operating Temperature (°C): 0 to +60	
--	--

Regulatory Compliance

RoHS 2015: Exempt	
Reach 224: Contains SVHC(s)	
Certificate of Conformance: View	
Country of Origin: United States	
Imported By: Edmund Optics India Private Limited	

Product Details

- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller (#18-645). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.

Note: 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.