


[See all 16 Products in Family](#)

Acetylene Fiber-Coupled Gas Cell, 3 cm Path Length, FC/APC



Stock **#72-204** [CONTACT US](#)

-

 1

+

 ₹50,400

ADD TO CART

Volume Pricing	
Qty 1+	₹50,400 each
Need More?	Request Quote

Product Downloads

3	Path Length (cm):
FC/APC	Fiber Connector Type:

General	
Acetylene (¹² C ₂ H ₂)	Type:
C2H2-12-H(3)-200-FCAPC	Model Number:

Optical Properties	
	Wavelength Range (nm):

1510 - 1540	
	Transmission (%):
>50	
Environmental & Durability Factors	
	Operating Temperature (°C):
+5 to +70	
Regulatory Compliance	
	Certificate of Conformance:
View	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Hydrogen Cyanide and Acetylene Gasses Available for Wavelength Coverage of 1510 to 1565nm
- FC and SC Fiber Connection Options with a Variety of Path Lengths Available
- NIST Traceable Reference Cells

Wavelength References Fiber-Coupled Gas Cells are FC/APC, SC/APC, FC/PC, or SC/PC connected fiber coupled, gas filled precision filters whose absorption wavelengths depend on specific molecular energy level transitions that may be used as wavelength standards. Hermetically sealed to maintain >10 year lifetime, these gas cells feature metal housings, wedged windows, and coated optics for minimum interference artifacts and can be easily integrated into existing benchtop systems. Wavelength References Fiber-Coupled Reference Cells are available with a variety of path lengths and pressures which meet the requirements of NIST Standard Reference Material® (SRMs) 2517a, 2519, or 2519a. Short path lengths are recommended for measuring gasses at high concentration while longer path lengths enable more sensitive measurements. These reference cells are ideal for spectroscopy, wavelength/frequency locking, laser calibration, and optical gas sensing systems. Hydrogen Cyanide (H¹³C¹⁴N) has been identified by national standards bodies as the primary wavelength reference in the C-band (1530 – 1565nm) while Acetylene (¹²C₂H₂) is recognized as a primary wavelength reference in the 1510 to 1540nm band.