

[See all 23 Products in Family](#)

# GS3-U3-89S6C-C 1" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera

See More by [Teledyne FLIR](#)



Teledyne FLIR IIS Grasshopper®3 USB 3.0 Cameras (Front)



Stock #36-338 **1 In Stock**

[Similar Cameras](#)

1 MRP ₹3,60,549

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹3,60,549 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

Color Spectrum:

## General

Color Camera Type:

GS3-U3-89S6C-C Model Number:

FLIR	<b>Manufacturer:</b>
Grasshopper®3	<b>Camera Series:</b>

**Note:**  
Dimensions: Exclude 1/4-20 Tripod Adapter and Lens Holder

## Physical & Mechanical Properties

44 x 29 x 57.5 (excludes connectors and lens mount)	<b>Dimensions (mm):</b>
90	<b>Weight (g):</b>
Full	<b>Housing:</b>

## Sensor

128MB	<b>Image Buffer:</b>
1"	<b>Sensor Format:</b>
8.90	<b>Resolution (Megapixels):</b>
43.00	<b>Frame Rate (fps):</b>
4,096 x 2,160	<b>Pixels (H x V):</b>
3.45 x 3.45	<b>Pixel Size, H x V (µm):</b>
14.13 x 7.45	<b>Sensing Area, H x V (mm):</b>
Sony IMX255	<b>Imaging Sensor:</b>
Progressive Scan CMOS	<b>Type of Sensor:</b>
Global	<b>Shutter Type:</b>
10/12 bit	<b>Pixel Depth:</b>
10µs - 32s	<b>Exposure Time:</b>
66.15 (Mode 0) / 71.13 (Mode 7)	<b>Dynamic Range (dB):</b>
USB3 Vision v1.0	<b>Machine Vision Standard:</b>

## Electrical

4.5	<b>Power Consumption (W):</b>
-----	-------------------------------

## Hardware & Interface Connectivity

USB 3.0	<b>Interface:</b>
USB 3.1 Gen 1, Micro-B with Screw Locks	<b>Connector:</b>
Power over USB (required for operation) <a href="#">#86-770</a> or via GPIO with <a href="#">#86-784</a>	<b>Power Supply:</b>
1 opto-isolated input, 2 opto-isolated outputs, 2 non-isolated bi-directional ports	<b>GPIOs:</b>
Hardware Trigger (GPIO) or Software Trigger	<b>Synchronization:</b>
Back Panel	<b>Interface Port Orientation:</b>
8-pin Hirose (HR25)	<b>GPIO Connector Type:</b>

## Threading & Mounting

C-Mount	<b>Mount:</b>
1/4-20 with Tripod Mount Adapter <a href="#">#88-057</a>	<b>Mounting Threads:</b>

## Environmental & Durability Factors

0 to +50 **Operating Temperature (°C):**

-30 to +60 **Storage Temperature (°C):**

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Certificate of Conformance:**  
[View](#)

**Reach 240:**  
[Contains SVHC\(s\)](#)

**Country of Origin:**  
Canada

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Feature High Resolution, High Sensitivity Sensors
- High Frame Rates Driven by USB 3.0 Interface
- Includes Image Capture Software and SDK



Teledyne  
Authorized  
Distributor

### Teledyne FLIR IIS Grasshopper®3: Machine Vision area scan camera

The **Grasshopper®3** offers a cost-effective, powerful and easy-to-use alternative to Camera Link and dual GigE LAG solutions.

The **Grasshopper®3** camera line combines the benefits of CCD with the affordability and data throughput of either USB 3.0 or GigE interfaces. This high-performance camera model provides a range of characteristics with either CMOS or CCD sensors. Its FPGA and frame buffer-based architecture provides optimal reliability, a rich set of features, and a full image processing pipeline including color interpolation, gamma, and lookup table functionality.

**Note:** USB 3.0 cable (sold separately) is required for operation. Optional power supply ([#86-784](#)) available. Software available for [download](#). FLIR was previously known as Point Grey.

#### Features

- Compact form factor
- USB 3.0 models with resolutions from 2.3 to 12 Megapixel sensors
- GigE interface model at 2.3 Megapixel for high bandwidth performance
- Various high-resolution, large format CCD and CMOS sensor options
- Color transformation tools for true-to-life color
- GigE models feature PoE for simplified setup and maintenance
- Spinnaker SDK and code samples

#### Applications

- Factory automation
- 3D Measurement
- Flat Panel Inspection
- Life science instrumentation
- Biometrics kiosk solutions
- Ophthalmology
- Intelligent traffic systems