

Green, 0.315" LED Spot Light

See More by [Advanced Illumination](#)



Stock **#87-543** CLEARANCE CONTACT US

-

1

+

₹11,741

ADD TO CART

Volume Pricing	
Qty 1+	₹11,741 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

SPECIFICATIONS

General

	Model Number:
SL-4301A-520-IC	
	LED Lifetime (hours):
50,000	

LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Spot Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
7.90	Diameter (mm):
1/4	Fiber Bundle Diameter (inches):
38.10	Length (mm):
0.312	Outer Diameter (inches):
Optical Properties	
Green	Color:
520.00	Wavelength (nm):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Power Supply:
1.5	Length of Cable (m):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

Required 24V power supply [#66-855](#) is sold separately. Units cannot be intensity controlled.

- Compatible with 8mm or ¼" (0.312") Fiber Illumination Ports
- 50,000 Hour Lifetime
- Low Power Consumption

Advanced Illumination Fiber Optic Replacement LED Spot Lights are specially designed to replace fiber optic light guides for fiber optic illumination systems used in microscopes or machine vision applications. The compact spot lights will directly replace any ¼" (0.312") fiber light guide or can be used with our light guide adapters to replace large fiber bundles. Advanced Illumination Fiber Optic Replacement LED Spot Lights are available in blue, green, red, and white. These spot lights are ideal for use with our [TECHSPEC® Telecentric Backlight Illuminator](#) or [In-Line Illumination Telecentric Lenses](#).

Note: Required 24V power supply [#66-855](#) is sold separately. Units cannot be intensity controlled.

TECHNICAL INFORMATION

0.315" LED Spot Light Dimensions



