

High Output L-Type Spot Light HLV3-22SW-4S

See More by [CCS](#)



Stock **#21-863** CLEARANCE 10 TO 12 DAYS

-

1

+

₹68,850

ADD TO CART

Qty 1+
₹68,850

Volume Pricing
Request Quote

Product Downloads

SPECIFICATIONS

General	
HLV3-22SW-4S	Model Number:
LED Illuminator	Type of Illumination:
	Manufacturer:

CCS	
Spot Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
22 x 46.6 x 49 (WxD xH), Tip diameter 8 mm	Dimensions (mm):
53	Weight (g):
6	Active Area (mm):
Optical Properties	
White	Color:
Electrical	
3.7	Power Consumption (W):
1000mA	Maximum Input Current:
Environmental & Durability Factors	
5600	Color Temperature (K):
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- Ideal for Alignment and Measurement Applications
- L-Type and Cylindrical Housing Options
- Available with 8mm or 12mm Tip

CCS LED Spot Light Illuminators provide high intensity output and uniform spot lighting in a lightweight and compact housing. Available in two configurations, the L-Type orients the LED at a right angle to save horizontal space in compact applications while the cylindrical type provides a higher output intensity in a longer overall housing. Both housing options are available with red, white, blue, green, and IR outputs. CCS LED Spot Light Illuminators are ideal for alignment of LCD's or circuit boards (PCB's), dimension measurement applications, or as a light source for spot illumination. 8mm diameter tip configurations integrate directly with [TECHSPEC® CompactTL™ Telecentric Lenses](#).