

Harsh Environment Transmission Dip Probe Tip, 2 mm

See More by [Ocean Optics](#)



Stock **#90-582** NEW CONTACT US

-

1

+

₹45,675

ADD TO CART

Volume Pricing	
Qty 1+	₹45,675 each
Need More?	Request Quote

Product Downloads

Construction Material:
Titanium

General

Model Number:
RT-TI-2MM

Optical Properties

Wavelength Range (nm):
200 - 2500

Regulatory Compliance

RoHS 2015:
Compliant
Certificate of Conformance:
View
Reach 250:
Compliant
Country of Origin:
United States
Imported By:
Edmund Optics India Private Limited

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV–VIS to VIS–NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).