

[See all 9 Products in Family](#)

High Contrast NIR Polarizing Film, 76mm x 76mm



High Contrast NIR Polarizing Film

Stock #25-104 **10 In Stock**

⊖ 1 ⊕ ₹34,254

ADD TO CART

Volume Pricing	
Qty 1-9	₹34,254 each
Qty 10+	₹27,481 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Note:
Delivered with protective film and paper overlayer on both sides marked to show polarization axis. Outer 0.5mm edge is not functional due to loss of transparency during laser cutting.

Physical & Mechanical Properties

Length (mm):

76.00	Dimensions (mm):
76.0 x 76.0 ±0.2	
0.50 (Nominal)	Thickness (mm):
Polarizing Film	Construction:
76.00	Width (mm):

Optical Properties

Uncoated	Coating:
>1000:1 (700nm-1600nm) >10000:1 AVG (400nm-800nm)	Extinction Ratio:
Cellulose Triacetate	Substrate: <input type="checkbox"/>
532nm: 65 830nm: 70 1550nm: 80	P-Polarization Transmission (%):
532nm: 0.002 830nm: 0.04 1550nm: 0.1	S-Polarization Transmission (%):
80-50	Surface Quality:
420 - 1600	Wavelength Range (nm):

Environmental & Durability Factors

85 x 500 (dry)	Heat Resistance (°C x Hours):
-40 x 500	Cold Resistance (°C x Hours):
DIN ISO 9022-2-10-07 DIN ISO 9022-2-11-05 DIN ISO 9022-2-12-07 DIN ISO 9022-2-14-05	Environmental Durability:
15-25	Storage Temperature (°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- >1,000:1 Extinction Ratio from 700nm-1600nm
- Ideal for NIR Imaging Applications
- Affordable Alternative to Conventional Glass Polarizers
- [Ultra-Broadband NIR Polarizing Films](#) also Available

High Contrast Near-Infrared (NIR) Polarizing Film provides excellent contrast in the VIS and NIR spectrum and is an affordable alternative to conventional glass polarizers. These polarizing films are designed for assisting stray light management with NIR photodetectors and glare reduction in industrial imaging applications. With 1,000:1 contrast in NIR and 10,000:1 contrast in VIS, these polarizing films have excellent broadband performance. High Contrast Near-Infrared (NIR) Polarizing Film features high transmission between 415 - 1600nm and can be easily cut to size. These polarizing films are ideal for the use in sensing, NIR imaging, and SWIR applications.

