

## High Frequency Optical Chopper



High Frequency Optical Chopper

Stock **#28-115** **1 In Stock**

1  MRP ₹3,35,592

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹3,35,592 each
--------	----------------

Need More?	<a href="#">Request Quote</a>
------------	-------------------------------

### Product Downloads

#### General

**Slot Variants Included:**  
445 (In Blade Protector)

**Note:**  
Compatible Discs: [#28-117](#), [#28-127](#), [#28-129](#),  
[#28-130](#)

#### Physical & Mechanical Properties

**Dimensions (mm):**  
Control Unit: 254 W x 76 H x 178 D  
Chopping Head: 32 W x 73 H x 75 L

Control Unit: 2.6 **Weight (kg):**

**Mark-Space Ratio:**  
1:1 When Using 1 Blade

## Optical Properties

**Temperature Coefficient @ 25°C (%/°C):**  
±0.01

## Electrical

**Frequency Stability (%):**  
Short Term: See blade specification for phase jitter  
Long Term: ±0.1% of maximum frequency

## Hardware & Interface Connectivity

**Connector:**  
0-5 VHCT TTL Pulse via BNC

**Operating Voltage (V):**  
100 - 130 or 200 - 260

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

**Country of Origin:**  
United Kingdom

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Range of Interchangeable Chopping Discs
- Frequencies Ranging from 5Hz to 110 kHz
- Manual or External Frequency Control

Optical Choppers are used to mechanically modulate light sources that pass through their discs. These optical choppers include a range of interchangeable discs from 2 to 200 slots for the standard chopper and 445 slots for the high frequency chopper, supporting frequencies up to 20kHz and up to 110kHz respectively. Chopping frequency can be adjusted by either a ten-turn dial or by applying an external DC voltage to the "Control In" BNC port on the front panel. Optical Choppers are ideal for use in a variety of applications including Lock-in Detection, Fluorescence Decay Measurement, Rotation Detection, and Reduction of Average Power. These choppers feature a "Reference Out" BNC port that provides a TTL pulse at the chopping frequency and in phase with the chopping action.

Please exercise caution when utilizing the high frequency chopper, #28-115, in applications where it is not possible to completely remove the danger of finger ingress. For safe operation a blanking plate is included to cover all unused apertures and to reduce the size of the aperture in use. High chopping frequencies also lead to heated jets of air to be released through any open apertures in the blade protector and operation is loud and should be considered for applications where noise is a concern. Please ensure the chopper head is securely bolted to the operating surface due to vibrations from the high chopping frequencies.

## Technical Information

