

[See all 64 Products in Family](#)

# IDS Imaging GV-5580FA-C-HQ 4.92 GigE Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ FAIP65/67 PoE Cameras (Front)



Stock **#26-308** CLEARANCE **1 In Stock**

-

1

+

MRP ₹73,160

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹73,160 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

|                |  |               |
|----------------|--|---------------|
| Color          |  | Spectrum:     |
| Color Camera   |  | Type:         |
| GV-5580FA-C-HQ |  | Model Number: |

|                                                                               |                             |
|-------------------------------------------------------------------------------|-----------------------------|
| IDS Imaging Development Systems                                               | Manufacturer:               |
| uEye+ FA                                                                      | Camera Series:              |
| Physical & Mechanical Properties                                              |                             |
| 41 x 53 x 42.7 (excludes connectors and lens mount)                           | Dimensions (mm):            |
| 173                                                                           | Weight (g):                 |
| Full                                                                          | Housing:                    |
| Sensor                                                                        |                             |
| 128MB                                                                         | Image Buffer:               |
| 1/2.5"                                                                        | Sensor Format:              |
| 4.92                                                                          | Resolution (Megapixels):    |
| 15.00                                                                         | Frame Rate (fps):           |
| 2,560 x 1,920                                                                 | Pixels (H x V):             |
| 2.20 x 2.20                                                                   | Pixel Size, H x V (µm):     |
| 5.63 x 4.22                                                                   | Sensing Area, H x V (mm):   |
| ON Semi MT9P006                                                               | Imaging Sensor:             |
| Progressive Scan CMOS                                                         | Type of Sensor:             |
| Rolling                                                                       | Shutter Type:               |
| 12 bit                                                                        | Pixel Depth:                |
| 30µs - 0.131s                                                                 | Exposure Time:              |
| Not Specified                                                                 | Dynamic Range (dB):         |
| GigE Vision                                                                   | Machine Vision Standard:    |
| Electrical                                                                    |                             |
| 1.6 - 2.6                                                                     | Power Consumption (W):      |
| Hardware & Interface Connectivity                                             |                             |
| GigE (PoE)                                                                    | Interface:                  |
| GigE M12, screwable                                                           | Connector:                  |
| Power over Ethernet (PoE) or 12 - 24VDC via GPIO with <a href="#">#19-692</a> | Power Supply:               |
| 2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground           | GPIOs:                      |
| Hardware Trigger (GPIO); Software Trigger                                     | Synchronization:            |
| Back Panel                                                                    | Interface Port Orientation: |
| 8-pin Binder                                                                  | GPIO Connector Type:        |
| Threading & Mounting                                                          |                             |
| C-Mount                                                                       | Mount:                      |
| 1/4-20 with Tripod Mount Adapter <a href="#">#19-694</a>                      | Mounting Threads:           |
| Environmental & Durability Factors                                            |                             |
| 0 to +55                                                                      | Operating Temperature (°C): |
| -20 to +60                                                                    | Storage Temperature (°C):   |

| Regulatory Compliance                                                                                                                                                                                   |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| <a href="#">Exempt</a>                                                                                                                                                                                  | RoHS 2015:                  |
| <a href="#">View</a>                                                                                                                                                                                    | Certificate of Conformance: |
| <a href="#">Contains SVHC(s)</a>                                                                                                                                                                        | REACH 241:                  |
| Germany                                                                                                                                                                                                 | Country of Origin:          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | Imported By:                |

## Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.