

TECHSPEC[®]

Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 25.4mm Dia., 6.35mm Thick



Stock #29-524 20+ In Stock

-

1

+

₹35,811

ADD TO CART

Volume Pricing	
Qty 1-5	₹35,811 each
Qty 6+	₹33,865 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
25.40 +0.00/-0.10	Diameter (mm):
6.35 ±0.10	Thickness (mm):
Commercial Polish	Edges:
	Bevel:

Protective as needed	
Optical Properties	
10-5	Surface Quality:
R _s > 99.50% @ 830 - 1010nm @ 45° AOI R _p > 99.50% @ 840 - 997nm @ 45° AOI	Coating Specification:
0 ±50 fs ² @ 830 - 1010nm @ 45° AOI(s-pol) 0±50 fs ² @ 861 - 966nm @ 45° AOI (p-pol)	GDD Specification:
λ/10	Surface Flatness (P-V):
830 - 1010	Design Wavelength DWL (nm):
0.75J/cm ² @ 920nm, 100-on-1, S-Polarization, 5Hz Pulse Duration 25fs, 350µm Dia.	Damage Threshold, Reference: □
Regulatory Compliance	
View	Certificate of Conformance:
Japan	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Femtosecond Laser Damage Threshold exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near 0fs² GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

Coating Curves