

[See all 76 Products in Family](#)

# IDS GV-5890CP-M-GL, GigE, 1/1.7" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ GigE Cameras



[+1](#)

Stock **#26-252** **1 In Stock**

-

1

+

MRP ₹61,360

Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹61,360 each                  |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

| Spectrum:         |  |
|-------------------|--|
| Monochrome        |  |
| General           |  |
| Type:             |  |
| Monochrome Camera |  |
| Model Number:     |  |
| GV-5890CP-M-GL    |  |

|                                                                               |                             |
|-------------------------------------------------------------------------------|-----------------------------|
| IDS Imaging Development Systems                                               | Manufacturer:               |
| uEye+ CP                                                                      | Camera Series:              |
| Physical & Mechanical Properties                                              |                             |
| 29 x 29 x 29 (excludes connectors and lens mount)                             | Dimensions (mm):            |
| 51                                                                            | Weight (g):                 |
| Full                                                                          | Housing:                    |
| Sensor                                                                        |                             |
| 128MB                                                                         | Image Buffer:               |
| 1/1.7"                                                                        | Sensor Format:              |
| 12.00                                                                         | Resolution (Megapixels):    |
| 10.00                                                                         | Frame Rate (fps):           |
| 4,000 x 3,000                                                                 | Pixels (H x V):             |
| 1.85 x 1.85                                                                   | Pixel Size, H x V (µm):     |
| 7.4 x 5.55                                                                    | Sensing Area, H x V (mm):   |
| Sony IMX226                                                                   | Imaging Sensor:             |
| Progressive Scan CMOS                                                         | Type of Sensor:             |
| Rolling                                                                       | Shutter Type:               |
| 12 bit                                                                        | Pixel Depth:                |
| 0.13ms - 2000ms                                                               | Exposure Time:              |
| 68.00                                                                         | Dynamic Range (dB):         |
| GigE Vision                                                                   | Machine Vision Standard:    |
| Electrical                                                                    |                             |
| 1.8 - 2.9                                                                     | Power Consumption (W):      |
| Hardware & Interface Connectivity                                             |                             |
| GigE (PoE)                                                                    | Interface:                  |
| GigE RJ45, screwable                                                          | Connector:                  |
| Power over Ethernet (PoE) or 12 - 24VDC via GPIO with <a href="#">#16-016</a> | Power Supply:               |
| 2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground           | GPIOs:                      |
| Hardware Trigger (GPIO); Software Trigger                                     | Synchronization:            |
| Back Panel                                                                    | Interface Port Orientation: |
| 8-pin Hirose connector (HR25-7TR-8PA(73))                                     | GPIO Connector Type:        |
| Threading & Mounting                                                          |                             |
| C-Mount                                                                       | Mount:                      |
| 1/4-20 with Tripod Mount Adapter <a href="#">#35-088</a>                      | Mounting Threads:           |
| Environmental & Durability Factors                                            |                             |
| 0 to +55                                                                      | Operating Temperature (°C): |
| -20 to +60                                                                    | Storage Temperature (°C):   |

| Regulatory Compliance                                                                                                                                                                                   |                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| <a href="#">Exempt</a>                                                                                                                                                                                  | RoHS 2015:                  |
| <a href="#">View</a>                                                                                                                                                                                    | Certificate of Conformance: |
| <a href="#">Contains SVHC(s)</a>                                                                                                                                                                        | REACH 241:                  |
| Germany                                                                                                                                                                                                 | Country of Origin:          |
| Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 | Imported By:                |

## Product Details

- Standard (SE) and Compact (CP) Housing Options Available
  - C-Mount with Large Format CMOS Sensors up to 1.1"
  - GenICam GigE Vision Compliant
  - [IDS Imaging uEye CP/XCP/SE USB3 Cameras](#) Available
- IDS Imaging uEye CP/SE GigE Cameras utilize IDS Imaging's [peak SDK platform](#) that supports GenICam and GigE Vision standards for ease of software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat sensitive applications. IDS Imaging uEye CP/SE GigE Cameras feature a screwable 8-pin Hirose connector for trigger and flash as well as two GPIOs. These cameras are ideal for a variety of applications such as automation, automotive, medical technology, and logistics.