

Coherent® LightSmyth™ 1040nm, 1000 Grooves/mm, 31.8 x 12.3mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock **#16-869** 10 TO 12 DAYS

- 1 + **₹53,505.00**

ADD TO CART

Qty 1+
₹53,505.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm): 1000
Groove Density Uniformity (grooves/mm): 0.001
Design Wavelength DWL (nm): 1040 ±20

Minimum Efficiency (%): ≥94 @ 1040nm
Dimensions (mm): 31.80 x 12.30
Angle of Incidence (°): 31.3 ±1
Clear Aperture CA (mm): 30.80 x 11.30
Coating: Dielectric
Construction: Multi-Layer Dielectric Binary Etch Grating
Length (mm): 31.80
Model Number: 1303874
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 60-40
Thickness (mm): 0.95 ±0.050
Type: Transmission Diffraction Grating
Width (mm): 12.30
Alignment of Grooves to Edge (°): 0.1 (typical)
Polarization: S and P
Note: S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View