

[See all 4 Products in Family](#)

Image Analysis Micrometer, NIST Certificate




Image Analysis Micrometers

Stock **#59-271** [CONTACT US](#)

1 MRP ₹1,18,944

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹1,18,944 each
Qty 5+	₹1,13,135 each
Need More?	Request Quote

Product Downloads

General

Note:
Patterns on Test Plate 1, 2 and 8 are NIST traceable and conforms to ASTM-E112.

NIST Certification:
Yes

Physical & Mechanical Properties

Scale Divisions:
0 to 2.5 inches

0.5 inches	Increments:
25.4 x 76.2	Dimensions (mm):
1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):
±2 (±4 for Plate 1 Item #3 and #4)	Pattern Tolerance (µm):

Optical Properties

Chrome on Glass	Substrate: <input type="checkbox"/>
60-40	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Designed for Morphological Calibration and Measurement
- 8 Test Plates of Various Patterns
- NIST Certified Version Available

Image Analysis Micrometers are ideal for morphological calibration and measurement of two-dimensional shapes. They feature eight test plates in various sizes of circles, squares, lines, and other geometries. Small patterns, featuring diameters as small as 6.25µm, are ideal for image analysis and machine vision systems, whereas larger features, including a 2.5" linear scale and 0.5" diameter circle, are available for macro inspection. Test plates 1-4 correspond to top patterns and 5-8 to bottom patterns from the left to right. Image Analysis Micrometers are available in NIST certified versions which conform to ASTM E112 requirements with plate 1, 2, and 8 measured and calibrated.

Technical Information




Plate	Frame Size	Description
1	4.6 x 3.5mm	Circles with 2.00, 1.00, 0.50, and 0.25mm diameter
2	1.0 x 0.8mm	Circles with 0.500, 0.250, 0.125, 0.0625mm diameter
3	1.0 x 0.8mm	7 bars separated by 30°, 0.200 x 0.020mm
4	1.0 x 0.8mm	Various circles, bars, and angular features
5	1.0 x 0.8mm	Squares of 0.100, 0.040, 0.020mm (2 sets)
6	2.05 x 1.65mm	Grid with 0.050mm lines at 0.100mm pitch
7	4.2 x 3.4mm	Grid with 0.200mm lines at 0.200mm pitch
8	10mm long	Scale with 0.010mm divisions