


## Image Analysis Micrometer on Opal Glass, NIST Certificate



Chrome on Opal Glass

Stock **#59-272** [CONTACT US](#)

1  MRP ₹1,24,785

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹1,24,785 each
Qty 5+	₹1,18,572 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Note:**  
Patterns on Test Plate 1, 2 and 8 are NIST traceable and conforms to ASTM-E112.

**NIST Certification:**  
Yes

### Physical & Mechanical Properties

**Scale Divisions:**  
0 to 2.5 inches

0.5 inches	<b>Increments:</b>
25.4 x 76.2	<b>Dimensions (mm):</b>
1.50 ±0.100	<b>Thickness (mm):</b>
±0.100	<b>Dimensional Tolerance (mm):</b>
±2 (±4 for Plate 1 Item #3 and #4)	<b>Pattern Tolerance (µm):</b>

## Optical Properties

Chrome on Opal Glass	<b>Substrate:</b> <input type="checkbox"/>
----------------------	--

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 235:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Designed for Morphological Calibration and Measurement
- 8 Test Plates of Various Patterns
- NIST Certified Version Available

Image Analysis Micrometers are ideal for morphological calibration and measurement of two-dimensional shapes. They feature eight test plates in various sizes of circles, squares, lines, and other geometries. Small patterns, featuring diameters as small as 6.25µm, are ideal for image analysis and machine vision systems, whereas larger features, including a 2.5" linear scale and 0.5" diameter circle, are available for macro inspection. Test plates 1-4 correspond to top patterns and 5-8 to bottom patterns from the left to right. Image Analysis Micrometers are available in NIST certified versions which conform to ASTM-E112 requirements with plate 1, 2, and 8 measured and calibrated.

## Technical Information




Plate	Frame Size	Description
1	4.6 x 3.5mm	Circles with 2.00, 1.00, 0.50, and 0.25mm diameter
2	1.0 x 0.8mm	Circles with 0.500, 0.250, 0.125, 0.0625mm diameter
3	1.0 x 0.8mm	7 bars separated by 30°, 0.200 x 0.020mm
4	1.0 x 0.8mm	Various circles, bars, and angular features
5	1.0 x 0.8mm	Squares of 0.100, 0.040, 0.020mm (2 sets)
6	2.05 x 1.65mm	Grid with 0.050mm lines at 0.100mm pitch
7	4.2 x 3.4mm	Grid with 0.200mm lines at 0.200mm pitch
8	10mm long	Scale with 0.010mm divisions