

TECHSPEC® Infinite Conjugate, DUV Coated, 15X/0.28NA RefIX Objective



Stock **#59-315** 10 TO 12 DAYS

⊖ 1 ⊕

₹193,923.00

ADD TO CART

Qty 1+
₹193,923.00
Qty 2+
₹171,303.00
Volume Pricing
Request Quote

Get Product Downloads

Entrance Pupil Position (mm):
7.4 (Diameter)

Horizontal Field of View, 1/2" Sensor:
0.43mm

Horizontal Field of View, 2/3" Sensor:
0.59mm

Focal Length FL (mm):
13.30

Coating: DUV Enhanced Aluminum (150-11000nm)
Magnification: 15X
Numerical Aperture NA: 0.28
Mounting Threads: RMS
Type: Microscope Objective
Obscuration (%): 27.00
Transmitted Wavefront, RMS: λ/10
Diameter of Small Mirror (mm): 8.8
Working Distance (mm): 23.75
Aperture Diameter (mm): 8.5
Note: Requires a 200mm secondary tube lens
Coating Specification: R _{avg} >83% @ 150 - 1000nm (typical) R _{avg} >94% @ 1000 - 11000nm (typical)
Wavelength Range (nm): 150 - 11000
Style: Infinity Corrected
Manufacturer: Edmund Optics®

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View