

LightPath 390010 | 4.5mm Dia., 0.83 NA, BBAR (8000-12000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock #88-073

10 TO 12 DAYS

-

1

+

₹31,320.00

ADD TO CART

Qty 1-10
₹31,320.00
Qty 11+
₹27,623.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
4.50 ±0.015

Effective Focal Length EFL (mm):
1.47 @ 9200nm

Numerical Aperture NA:
0.83

Substrate:

Black Diamond™ BD-2 (Ge ₂₈ Sb ₁₂ Se ₆₀)
Aspheric Design Wavelength (nm): 9200
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <1.0% @ 8 - 12μm
Surface Quality: 80-50
Clear Aperture CA (mm): 3.00
Edge Thickness ET (mm): 1.63
Center Thickness CT (mm): 2.17
f#: 0.6
Bevel: Protective bevel as needed
Density (g/cm³): 4.68
Index of Refraction n _d @ 10μm: 2.6023
Index of Refraction n _d @ 14μm: 2.5843
Index of Refraction n _d @ 4μm: 2.6210
Index of Refraction n _d @ 5μm: 2.6173
Lightpath Lens Code: 390010
Thermo-optic coefficient dn/dT: 70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)
Transformation Temperature (°C): 285.00
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Working Distance (mm): 0.63
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant