

Coherent® LightSmyth™ 1060nm, 1600 Grooves/mm, 12.3 x 12.3mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock **#16-872** 10 TO 12 DAYS

- 1 + **₹32,625.00**

ADD TO CART

Qty 1+
₹32,625.00
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
1600

Groove Density Uniformity (grooves/mm):
0.001

Design Wavelength DWL (nm):
1060 ±20

Minimum Efficiency (%) : ≥94 @ 1060nm
Dimensions (mm) : 12.30 x 12.30
Angle of Incidence (°) : 58 ±1
Clear Aperture CA (mm) : 11.30 x 11.30
Coating : Dielectric
Construction : Multi-Layer Dielectric Binary Etch Grating
Length (mm) : 12.30
Model Number : 1304198
Substrate :  Fused Silica (Corning 7980)
Surface Quality : 60-40
Thickness (mm) : 0.95 ±0.050
Type : Transmission Diffraction Grating
Width (mm) : 12.30
Alignment of Grooves to Edge (°) : 0.1 (typical)
Polarization : S
Note : S-Polarization defined with E-field parallel to the grating grooves

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View