

[See all 16 Products in Family](#)

Coherent® LightSmyth™ 1525 - 1565nm, 966.18 Grooves/mm, 27 x 10mm Transmission Diffraction Grating

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock **#16-875** [CONTACT US](#)

-

1

+

₹45,844

ADD TO CART

Volume Pricing	
Qty 1+	₹45,844 each
Need More?	Request Quote

Product Downloads

General	
1304279	Model Number:
Transmission Diffraction Grating	Type:
Note: S-Polarization defined with E-field parallel to the grating grooves	

Physical & Mechanical Properties	
0.001	Groove Density Uniformity (grooves/mm):
27.00 x 10.00	Dimensions (mm):
26.00 x 9.00	Clear Aperture CA (mm):
Multi-Layer Dielectric Binary Etch Grating	Construction:
27.00	Length (mm):
0.68 ±0.050	Thickness (mm):
10.00	Width (mm):
0.1 (typical)	Alignment of Grooves to Edge (°):

Optical Properties	
966.18	Groove Density (grooves/mm):
1525 - 1565	Wavelength Range (nm):
≥92	Minimum Efficiency (%):
48.3 ±1	Angle of Incidence (°):
Dielectric	Coating:
Fused Silica (Corning 7980)	Substrate: □
60-40	Surface Quality:
S and P	Polarization:

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Importer:

Product Details

- High Diffraction Efficiency (>94% Absolute) and Low Scatter
- Polarization Independent and Single Polarization Optimized Gratings
- Robust Inorganic Materials for Superior Power Handling and Reliability
- Designs for NIR Wavelengths between 800 - 1800nm

Coherent® LightSmyth™ Transmission Diffraction Gratings are manufactured through a precision lithographic wafer-scale fabrication process and provide excellent optical performance, low polarization sensitivity, and low scatter. These gratings have a high diffraction efficiency of ≥94%, minimizing optical losses when used in multi-pass configurations. Gratings designed for near infrared (NIR) wavelengths between 800 - 1800nm are available with all featuring a precision line density uniformity of 0.001 lines/mm. Coherent® LightSmyth™ Transmission Diffraction Gratings are used in demanding applications including Spectral Beam Combining (SBC), LiDAR, optical telecommunications, pulse compression of pico- and femtosecond pulses, and spectroscopy. These gratings contain no organic materials and can be used with high power lasers and in environments up to 500 °C with no effects on performance. Please contact us for custom sizes or OEM requirements.

Note: II-VI Incorporated is now Coherent Corp.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we

provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
