

[See all 186 Products in Family](#)

Hoya IR76N (760nm), 50.8mm Sq., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock #66-069 **20+ In Stock**

1 MRP ₹10,594

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | ₹10,594 each |
| Qty 11-49 | ₹9,182 each |
| Need More? | Request Quote |

Product Downloads

General

Longpass Filter **Type:**

Physical & Mechanical Properties

50.8 x 50.8 **Dimensions (mm):**

50.80 **Length (mm):**

| | |
|----------------------|------------------------------------|
| 2.50 ±0.2 | Thickness (mm): |
| 50.80 | Width (mm): |
| ±0.38 | Dimensional Tolerance (mm): |
| Protective as needed | Bevel: |

Optical Properties

| | |
|----------------------------|--|
| 760±9 | Cut-Off Position λ_c (nm): |
| 760.00 ±9 | Cut-On Wavelength (nm): |
| Hoya IR76N | Glass/Filter Number: |
| Colored Glass | Substrate: <input type="checkbox"/> |
| Uncoated | Coating: |
| Black | Color: |
| 80-50 | Surface Quality: |
| IR | Wavelength: |
| 0.92 | Reflection Factor P_d: |
| <60 | $\Delta\lambda$ (nm): |
| N/A | TH (%): |

Material Properties

| | |
|------|---|
| 2.84 | Density (g/cm³): |
| 495 | Transformation Temperature (°C): |

Regulatory Compliance

| | |
|---|------------------------------------|
| Exempt | RoHS 2015: |
| Compliant | Reach 224: |
| View | Certificate of Conformance: |
| United States | Country of Origin: |
| Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | Imported By: |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- UV, VIS and IR Pass Ranges
- VIS Can Be Used for Color Bandpass
- Also Available [Mounted](#)

Hoya Colored Glass Longpass Filters feature a colored glass substrate. These filters are manufactured from substrates with inherently different absorption and transmission properties across a specific spectral region. Hoya Colored Glass Longpass Filters have UV, VIS, and IR pass ranges. A longpass filter has low transmission in the shortwave region (stopband) and high transmission in the longwave region (passband). These filters are also available in a [mounted](#) version.

Longpass Filter Kits

Longpass filter kits are available in three different options: UV-MS, MS, or MS-NIR. Each kit contains 8 filters in either 12.5mm diameter, 1" diameter, or 2" square.

UV-MS Kit Contains: WG 295, WG 305, WG 320, L 37, GG 400, GG 420, GG 435, GG 455

MS Kit Contains: GG 475, GG 495, OG 515, OG 530, OG 550, OG 570, OG 590, RG 610

MS-NIR Kit Contains: RG 630, RG 665, RG 695, RG 715, RG 780, RG 830, RG 850, RG 1000

Complete Filter Kits


Complete filter kits are available with 12.5mm diameter, 50.0mm diameter, 1" diameter, or 2" square filters. Each kit contains all 37 Longpass Glass Color Filter types.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Filter Simulation Software

[Click here](#) to download HOYA's colored glass filter simulation software which can be used to calculate the internal transmittance and external transmission of each HOYA glass type. The software can simulate the performance of individual filters with user specified thickness.

Technical Information



| | |
|-------------|---|
| λ_s | limit of stopband: specified at 0.001% internal transmittance |
| λ_c | cut-off position: specified at 50% internal transmittance |
| λ_p | limit of the passband |
| t_{ip} | internal spectral transmittance at λ_p |
| ρ | density |
| T_g | transformation temperature |

Compatible Mounts