

Image Analysis Micrometer




Image Analysis Micrometers

Stock **#53-713** **2 In Stock**

-

1

+

₹40,680

ADD TO CART

Volume Pricing	
Qty 1-4	₹40,680 each
Qty 5+	₹38,682 each
Need More?	Request Quote

Product Downloads

General

No

NIST Certification:

Physical & Mechanical Properties

0 to 2.5 inches

Scale Divisions:

0.5 inches

Increments:

Dimensions (mm):

25.4 x76.2	
1.50 ±0.100	Thickness (mm):
±0.100	Dimensional Tolerance (mm):
±2 (±4 for Plate 1 Item #3 and #4)	Pattern Tolerance (µm):

Optical Properties

Chrome on Glass	Substrate:
60-40	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Designed for Morphological Calibration and Measurement
- 8 Test Plates of Various Patterns
- NIST Certified Version Available

Image Analysis Micrometers are ideal for morphological calibration and measurement of two-dimensional shapes. They feature eight test plates in various sizes of circles, squares, lines, and other geometries. Small patterns, featuring diameters as small as 6.25µm, are ideal for image analysis and machine vision systems, whereas larger features, including a 2.5" linear scale and 0.5" diameter circle, are available for macro inspection. Test plates 1-4 correspond to top patterns and 5-8 to bottom patterns from the left to right. Image Analysis Micrometers are available in NIST certified versions which conform to ASTM-E112 requirements with plate 1, 2, and 8 measured and calibrated.

Technical Information




Plate	Frame Size	Description
1	4.6 x 3.5mm	Circles with 2.00, 1.00, 0.50, and 0.25mm diameter
2	1.0 x 0.8mm	Circles with 0.500, 0.250, 0.125, 0.0625mm diameter
3	1.0 x 0.8mm	7 bars separated by 30°, 0.200 x 0.020mm
4	1.0 x 0.8mm	Various circles, bars, and angular features
5	1.0 x 0.8mm	Squares of 0.100, 0.040, 0.020mm (2 sets)
6	2.05 x 1.65mm	Grid with 0.050mm lines at 0.100mm pitch
7	4.2 x 3.4mm	Grid with 0.200mm lines at 0.200mm pitch
8	10mm long	Scale with 0.010mm divisions