

Coherent® EnergyMax 1110743 | 25μJ-50mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#66-279** [CONTACT US](#)

-

1

+

₹1,60,650

ADD TO CART

Volume Pricing	
Qty 1+	₹1,60,650 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
J-25MB-LE Coherent Part Number: 1110743	
Type:	
Meter required	
Linearity (%):	
±3	
Calibration Uncertainty (%):	
±2	

<1	Noise Equivalent Energy (μJ):
	Compatible Meters:
#35-203, #66-277, #88-412	

Maximum Incident Energy Density: 500mJ/cm ² (10ns, 1064nm)	
25μJ - 50mJ	Energy Range:
	Preferred Meter:
#66-277	

Physical & Mechanical Properties

Active Area Diameter (mm):	
25	

Optical Properties

Calibration Wavelength (nm):	
1064	
Maximum Pulse Width (μs):	
17	

Wavelength Range (nm):	
190 - 12000	

Sensor

Type of Sensor:	
Pyroelectric	

Electrical

Maximum Repetition Rate (pps):	
1000	
Maximum Incident Beam Power (W):	
5	

Hardware & Interface Connectivity

Connector:	
DB25	
Length of Cable (m):	
2.5	

Regulatory Compliance

RoHS 2015:	
Exempt	
Reach 224:	
Contains SVHC(s)	

Certificate of Conformance:	
View	

Country of Origin:	
United States	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.