

[See all 15 Products in Family](#)

Coherent® EnergyMax 1191441 | 50μJ - 50mJ, USB

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#88-424** **2 In Stock**

MRP ₹3,00,546

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,00,546 each
Need More?	Request Quote

Product Downloads

General

Model Number:
 J-25MB-LE
 Coherent Part Number: 1191441

Type:
 Meterless

Linearity (%):
 ±3

Calibration Uncertainty (%):
 ±2

Noise Equivalent Energy (μJ):

<5

Maximum Incident Energy Density:
500mJ/cm² (10ns, 1064nm)

Energy Range:

50 μJ - 50mJ

Physical & Mechanical Properties

Active Area Diameter (mm):

25

Optical Properties

Calibration Wavelength (nm):

1064

Maximum Pulse Width (μs):

17

Wavelength Range (nm):

190 - 12000

Sensor

Type of Sensor:

Pyroelectric

Electrical

Maximum Repetition Rate (pps):

1000

Maximum Incident Beam Power (W):

5

Hardware & Interface Connectivity

Connector:

USB

Length of Cable (m):

3.0

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Reach 224:

[Contains SVHC\(s\)](#)

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.