

λ/4 920-1240nm, Polymer Achromatic Retarder



Stock **#49-235** 10 TO 12 DAYS

- 1 + **₹95,700.00**

ADD TO CART

Qty 1-5
₹95,700.00
Qty 6+
₹85,086.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
10.16

Diameter (mm):
25.40

Substrate: ☐
[N-BK7](#)

Operating Temperature (°C):
-20 to +50

Reflection (%) : 0.5
Retardance : λ/4
Surface Quality : 40-20
Thickness (mm) : 6.35
Thickness Tolerance (mm) : ±0.508
Type : Achromatic Waveplate
Dimensional Tolerance (mm) : ±0.127
Construction : Birefringent Polymer Stack
Transmitted Wavefront, P-V : λ/4 @ 632.8nm
Retardance Tolerance : λ/100
Beam Deviation (arcmin) : 1.00
Mount Thickness (mm) : 6.35
Wavelength Range (nm) : 920 - 1240
Damage Threshold, By Design : ☐ 500 W/cm²

Regulatory Compliance

RoHS 2015 : Compliant
Reach 209 : Compliant
Certificate of Conformance : View