

[See all 37 Products in Family](#)

Intensity Adjustment Dimmer for Effilux LED Lights



Stock **#75-337** NEW **1 In Stock**

-

1

+

₹24,638

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹24,638 each
Need More?	Request Quote

Product Downloads

General	
EFFI-DIMMER2	Model Number:
Accessory	Type:
Note: Provides intensity adjustment for every Effilux light using M12/M12P connectors	
Manufacturer:	

Effilux	
Hardware & Interface Connectivity	
24	Input Voltage (V):
0-5 or 0-24	Output Voltage (V):
Input/Output Options: Input: One M12 Male Output: Two M12 Female (multimode or dimming options)	
Regulatory Compliance	
View	Certificate of Conformance:
France	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details

- Direct Access to Optics for Quick, Manual Adjustment of Illumination Cone Angles
- Included Interchangeable Windows Allows for Easy Adjustment of Light Diffusion
- Easy to Integrate Linescan Accessory for Linear or Darkfield Lighting

Effilux Adjustable LED Bar Lights provide versatility by allowing the emission angle of the light to be modified by the user. Various illumination emission angles can be modified by simply removing the LED window that's held in place by screws to access the lens array and adjust the lens array height to one of the three indicated positions. Effilux Adjustable LED Bar Lights include three interchangeable windows: transparent, semi-diffuse, and opaline. By placing the optional polarizer or linescan accessories beneath the transparent window, glare can be eliminated or linear lighting created. The flexibility and ease of user modifications for these bar lights make them ideal for use in many application types.

Note: 24V power supply and M12 female to male cable are required. When first powered, these lights start in their Overdriven state with 700% intensity then relax to normal intensity.

3D-Printable Mount Files



Bar or Line Light Configuration

DOWNLOAD
NOW

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is

based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mbunts for Machine Vision Applications

[Read](#)



Video

Assembly of 3D Printed Mbunts for Common Illumination Geometries

[Watch](#)