

[See all 77 Products in Family](#)

LightPath 354525 | 6.65mm Dia., 0.44 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#19-702** **8 In Stock**

-

1

+

₹7,290

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,290 each
Qty 11-49	₹6,255 each
Need More?	Request Quote

Product Downloads

General	
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7	
Lightpath Lens Code: 354525	
Typical Applications: Collimate or Focus Laser Light	
Physical & Mechanical Properties	

6.65 ±0.015	Diameter (mm):
5.75	Clear Aperture CA (mm):
1.82	Edge Thickness ET (mm):
3.02 ±0.03	Center Thickness CT (mm):
Protective as needed	Bevel:
4.25	Distance from Window to Lens (D) (mm):

Optical Properties	
6.70 @ 515nm	Effective Focal Length EFL (mm):
0.44	Numerical Aperture NA:
D-ZK3	Substrate: 
±1	Focal Length Tolerance (%):
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
60-40	Surface Quality:
1.01	f#:
600 - 1050	Wavelength Range (nm):
4.9	Working Distance (mm):
Infinite	Conjugate Distance:
<0.05	Transmitted Wavefront Error (λ, RMS):

Environmental & Durability Factors	
≤200	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;