

[See all 7 Products in Family](#)

Lightpath 7100338 | 19mm FL, f/1.1, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock #15-691 **1 In Stock**

⊖ 1 ⊕ ₹37,440

ADD TO CART

Volume Pricing

Qty 1+	₹37,440 each
Need More?	Request Quote

Product Downloads

General

Thickness: 0.70mm
Material: Si

Compatible Window:

7100338

Lightpath Lens Code:

Physical & Mechanical Properties

17.84

Clear Aperture CA (mm):

Construction:
Matte Black Anodized Aluminum Housing

25.50 Length (mm):

24.00 Front Diameter (mm):

Optical Properties

19.00 Effective Focal Length EFL (mm):

Black Diamond™ BD-6 Substrate: □

1.1 f#:

BBAR (8000-12000nm) Coating:

8000 - 12000 Wavelength Range (nm):

R_{avg} <0.75% @ 8000 - 12,000nm Coating Specification:

2.7816 Index of Refraction (n_d) @ 10μm:

2.7683 Index of Refraction (n_d) @ 14μm:

2.7978 Index of Refraction (n_d) @ 4μm:

10.08 Working Distance (mm):

Sensor

Recommended Detector Format (H x V/Pixel Size):
640 x 480 / 17μm

Threading & Mounting

M25 x 0.5 Mounting Threads:

8.00 Thread Length (mm):

Material Properties

22.5 Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

30.5 x 10⁻⁶ @ 10μm Thermo-optic coefficient dn/dT:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

China Country of Origin:

Edmund Optics India Private Limited Imported By:

Product Details

- Precision Molded Chalcogenide Lenses
- Compact Designs for Thermal Imaging Cameras
- Focal Lengths from 2.7 to 24mm

Lightpath® Thermal Imaging Assemblies are a cost-effective alternative to diamond turned infrared lenses for applications in the mid-wave infrared (MMR) or long-wave infrared (LWIR). These lenses are molded from BD6™, a chalcogenide glass that offers high transmission from 1 to 15μm and is also optically athermalized from -40 to +85°C. These lenses feature a broadband antireflection coating from 8 to 12μm and are mounted in compact black anodized aluminum housings that are threaded to allow for adjustable focus. Lightpath Thermal Imaging Assemblies are ideal for medical diagnostics, gas sensing, thermography, thermal imaging, security, and manufacturing process control applications. Lenses with focal lengths from 2.7 to 24mm are available, covering detector sizes from 80 x 80 to 640 x 480 pixels.