

Lightpath 7100350 | 15mm FL, f/1.0, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock #15-689 CLEARANCE 10 TO 12 DAYS

-

1

+

 ₹18,004.65

ADD TO CART

Qty 1+
₹18,004.65

Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm): 15.00
Substrate: ☐ Black Diamond™ BD-6
f/#: 1.0
Coating: BBAR (8000-12000nm)
Wavelength Range (nm): 8000 - 12000

Clear Aperture CA (mm): 15.10
Coating Specification: R _{avg} <0.75% @ 8000 - 12,000nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 22.5
Compatible Window: Thickness: 0.70mm Material: Si
Construction: Matte Black Anodized Aluminum Housing
Index of Refraction n_d @ 10µm: 2.7816
Index of Refraction n_d @ 14µm: 2.7683
Index of Refraction n_d @ 4µm: 2.7978
Length (mm): 18.67
Lightpath Lens Code: 7100350
Mounting Threads: M25 x 0.5
Thermo-optic coefficient dn/dT: 30.5 x 10 ⁻⁶ @ 10µm
Working Distance (mm): 11.24
Front Diameter (mm): 24.00
Thread Length (mm): 7.00
Recommended Detector Format (H x V/Pixel Size): 384 x 288 / 17µm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant