


Low Noise Variable Voltage Amplifier



#90-634 Low Noise Variable Voltage Amplifier

Stock #90-634 NEW **1 In Stock**

MRP ₹2,75,058

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹2,75,058 each
Need More?	Request Quote

Product Downloads

Cut-Off Frequency (Hz):
 Lower: DC/1.5
 Upper: 10

General

Remote Control:
 Yes

Note:
 Includes:
 LEMO® 3-pin connector
 Datasheet

Electrical

7 x 10⁻¹⁰ Voltage Noise, High Gain (V/Hz^{1/2}):

40/60/80/100 (Switchable) Gain (dB):

1000 Input Impedance (kΩ):

Hardware & Interface Connectivity

±10 V (@ 100 kΩ Load) Output Voltage (V):

Power Supply:
Power Supply Required and Sold Separately:
USA: [#59-180](#)
Europe: [#59-180](#)
Japan: Not Available
Korea: Not Available
China: [#59-180](#)

50 Ω, BNC Output Type:

1 MΩ, BNC Input Type:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

Germany Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- High-Precision, Low-Frequency Signal Amplification with Constant Bandwidth Performance
- Low DC Offset Drift for Long-Term Measurement Stability
- AC/DC Coupling Options

Low-Frequency Voltage Amplifiers provide variable amplification of DC to 100kHz signals, allowing precise control over signal gain in sensitive measurement applications. Their low-noise design and wide gain range preserve signal fidelity across amplification settings, ensuring accurate voltage measurements even at high gain. By maintaining stable performance with minimal DC offset drift, these amplifiers improve measurement clarity, repeatability, and reliability in demanding laboratory and industrial settings. Low-Frequency Voltage Amplifiers feature switchable AC/DC coupling and remote control capability, providing flexibility for integration into automated systems or standalone setups. These amplifiers are ideal for sensor readout, low-level signal detection, and precise data acquisition across a wide range of scientific and engineering applications.

Note: Power supply sold separately. Please see specifications for more details.