

[See all 4 Products in Family](#)

LS-WL1 Laser Driven White Light Source Kit



Fiber Coupled Laser-Driven White Light Source



Stock **#23-881** 1 In Stock

-

1

+

MRP ₹3,43,557

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,43,557 each
Need More?	Request Quote

Product Downloads



General

LS-WL1	Model Number:
1 - 100%	Intensity Control Option:
>10,000	Lamp Lifetime (hours):
Note:	

Software, power supply, USB cable, and 1mm core fiber are included.	
Operating Modes:	
Constant output: CW	
Stroboscope: Frequency 0.12 Hz–200 kHz Duty cycle 0–100%	
Pulse trigger: Pulse width: 10µs–4000ms Delay: 4µs–4000ms (Width + Delay <= 4000ms)	
Direct mode: Analog/digital modulation to 100 kHz	
Note: All modes allow output setting of 1–100%	
Physical & Mechanical Properties	
Dimensions (mm):	
125 x 110 x 60	
Weight (kg):	
0.45	
Optical Properties	
Wavelength Range (nm):	
440 - 750	
Electrical	
Output Power (mW):	
500mW from 1mm fiber (0.5NA)	
Voltage (V):	
12	
Power Consumption (W):	
20 @ 100% Power	
Hardware & Interface Connectivity	
Connector:	
SMA	
Computer Interface:	
RS232 via USB	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 233:	
Compliant	
Country of Origin:	
Germany	
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	


Product Details

- Extremely High Luminance with Output Power up to 500mW
- Light Coupling with 50µm – 1mm Core Diameter Multimode Fibers
- User-Friendly GUI for Remote Control via USB or RS-232
- 450 – 700nm Wavelength Range

Fiber Coupled Laser-Driven White Light Source utilizes a 450nm laser pumped stable ceramic phosphor converter to produce a highly efficient and extremely bright light source with output power up to 500mW from a 1mm fiber. Featuring a broad 450 – 700nm spectral output, this light source can achieve switching frequencies up to 200kHz to act as a high-frequency stroboscope. The switching frequency and duty cycle can be controlled either via the jog-wheel or through the user-friendly software interface. Fiber Coupled Laser-Driven White Light Source's highly efficient optical coupling is suitable for use with multimode fibers of 50µm to 1mm and an NA up to 0.50. The high-power white light is up to 100X higher luminance than white LEDs, has a 10,000 hour lifetime through highly efficient cooling, and features simple control via USB or RS-232. This light source is ideal for biomedical and imaging applications including excitation for fluorescence or chemical surface processing, high speed spectroscopy, and high-resolution microscopy.

Note: Software, power supply, USB cable, and 1mm core fiber are included.

Technical Information



;