

[See all 9 Products in Family](#)

## L2-GM-02K05B-00-A, DALSA Linea Lite Line Scan GigE Camera

See More by [Teledyne DALSA](#)



Teledyne Imaging DALSA Linea Lite GigE Line Scan Cameras - Front



Stock #71-774 [CONTACT US](#)

⊖ 1 ⊕ MRP ₹78,057

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹78,057 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

**Spectrum:**  
Monochrome

### General

**Type:**  
Monochrome Camera

**Model Number:**  
L2-GM-02K05B-00-A

Teledyne DALSA	<b>Manufacturer:</b>
LINEA™LITE	<b>Camera Series:</b>
2048.00	<b>Resolution (Pixels):</b>
<b>Physical &amp; Mechanical Properties</b>	
46 x 46 x 37 (excludes connectors and lens mount)	<b>Dimensions (mm):</b>
111	<b>Weight (g):</b>
Full	<b>Housing:</b>
<b>Sensor</b>	
14.00 x 14.00	<b>Pixel Size, H x V (µm):</b>
DALSA Line Scan CMOS	<b>Type of Sensor:</b>
8/12 bit	<b>Pixel Depth:</b>
72.00	<b>Dynamic Range (dB):</b>
GigE Vision	<b>Machine Vision Standard:</b>
8.5	<b>Read Noise (e<sup>-</sup>):</b>
50	<b>Maximum Line Rate (kHz):</b>
30	<b>Full Well Depth (ke<sup>-</sup>):</b>
<b>Electrical</b>	
<5.0	<b>Power Consumption (W):</b>
<b>Hardware &amp; Interface Connectivity</b>	
GigE (PoE)	<b>Interface:</b>
GigE, RJ45 with Screw Locks	<b>Connector:</b>
+12 to +24V DC HD15 Connector or 48V POE	<b>Power Supply:</b>
Back Panel	<b>Interface Port Orientation:</b>
HD15 (High Density)	<b>GPIO Connector Type:</b>
<b>Threading &amp; Mounting</b>	
M42-Mbunt	<b>Mount:</b>
<b>Environmental &amp; Durability Factors</b>	
-10 to +65	<b>Operating Temperature (°C):</b>
<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>
Canada	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Compact 46 x 46mm Form Factor
- Line Rates from 12.5 – 50kHz
- 2k, 4k, or 8k Resolution Options Available

- Simple Integration with Gigabit Ethernet Connectivity
- Teledyne TurboDrive™ Enabled
- Monochrome and Color Options Available

Teledyne DALSA Linea Lite GigE Line Scan Cameras utilize a single line of sensor pixels to build up a two-dimensional image at a lower cost than area scan cameras. Featuring Teledyne DALSA's proprietary TurboDrive™ technology, these cameras can sustain line rates up to 50 kHz (and up to 64 kHz in burst mode) without straining your GigE network. With a compact 46 x 46mm form factor that is 45% smaller than the standard Linea line, these cameras are perfect for space-constrained setups. Teledyne DALSA Linea Lite GigE Line Scan Cameras feature higher dynamic ranges than alternative image capture methods and are available with 2k, 4k, or 8k resolutions. The 8k variants utilize two 4k/7µm pixel rows with a ½ pixel offset and allow for data from the two 4k/7µm images to be captured and reconstructed to achieve an image resolution of 8k/3.5µm in real time, which greatly facilitates the detectability of subpixel defects. These cameras are ideal for automated optical inspections, sorting systems, materials grading and inspections, and general-purpose machine vision applications. Download this [whitepaper](#) for more information on applications that would benefit from line scan camera technology.

**Note:** An H15 cable is required for GPIO operation and is not included with these cameras.

**Sapera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.