

Laser ZX20 640nm 30mW, 45°



Stock **#19-431** [CONTACT US](#)

-

1

+

₹99,450

ADD TO CART

Volume Pricing	
Qty 1-9	₹99,450 each
Qty 10+	₹89,550 each
Need More?	Request Quote

Product Downloads



General

2M

Laser Class - IEC:

Power Supply:[#24-361](#)
M12 Cable: [#64-836](#)

Note:

Homogeneous Line (Fine Line)

Style:

Z-Laser

Manufacturer:

Diode	Type of Laser:
	II
Laser Class - CDRH:	
Physical & Mechanical Properties	
90	Weight (g):
97	Housing Length (mm):
20	Housing Diameter (mm):
<0.8	Bore Sighting (mrad):
<10	Pointing Stability (µrad/°C):
Optical Properties	
640.00	Wavelength (nm):
Red	Color:
45.00	Fan Angle (°):
100mm to Collimation	Focus Range (mm):
Electrical	
30	Output Power (mW):
±3	Power Stability (%):
400	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
Free Space	Output Type:
5 pins, M12	Connector:
5 - 30 DC	Input Voltage (V):
Environmental & Durability Factors	
-10 to +50	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Homogenous Intensity Distribution Lines with Fan Angles from 20° to 90°
- IP67 Rated Stainless Steel Housing
- Violet, Blue, Green, and Red Wavelengths Available

Z-Laser ZX20 Focusable Machine Vision Laser Diode Modules feature even-intensity distribution lines in wavelengths from 405 – 660nm for demanding image processing applications. The IP67 rated, stainless steel housings are shock and vibration proof, enabling these laser diode modules to be used in harsh industrial environments. Manually focusable without any additional tools, Z-Laser ZX20 Focusable Machine Vision Laser Diode Modules are ideal for use in measurement and alignment in machine vision, 3D measurement, positioning, and triangulation applications. Additional features include 400kHz TTL modulation for camera synchronization, analog modulation for output power adjustment, and a serial interface for monitoring temperature, laser usage, and failure codes.

Note: M12 connection cable [#64-836](#) is recommended for ease of system integration.

Red wavelengths (640 and 660nm) are most commonly used in machine vision applications, as the quantum efficiency of most camera sensors are optimized for this wavelength range. Violet (405nm), blue (450nm), and green (520nm) are most commonly used with semi-transparent surfaces or with highly reflective surfaces such as polished metal and solder joints. These wavelengths can also be used to create visual contrast on glowing materials such as molten steel.