

[See all 35 Products in Family](#)

M2420, 2/3" Monochrome, DALSA Genie Nano GigE PoE Camera

See More by [Teledyne DALSA](#)



Teledyne DALSA Genie™ Nano GigE Cameras



Stock **#34-962** **7 In Stock**

[Similar Cameras](#)

⊖ 1 ⊕ MRP ₹1,08,855

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,08,855 each
Need More?	Request Quote

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

G3-GM11-M2420

Model Number:

Teledyne DALSA **Manufacturer:**

Genie Nano-1GigE **Camera Series:**

Windows, Linux, or 3rd party GenICam compliant SDK **Software:**

Physical & Mechanical Properties

40.6 x 29.0 x 44.0 (includes connectors and lens mount) **Dimensions (mm):**

46 **Weight (g):**

Full **Housing:**

Sensor

90MB **Image Buffer:**

2/3" **Sensor Format:**

5.00 **Resolution (Megapixels):**

23.80 **Frame Rate (fps):**

35.00 **Frame Rate - Burst Mode (fps):**

2,448 x 2,048 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (μm):**

8.45 x 7.07 **Sensing Area, H x V (mm):**

Sony IMX264 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/12 bit **Pixel Depth:**

Programmable or via external trigger **Exposure Time:**

76.4 **Dynamic Range (dB):**

GigE Vision v1.2 **Machine Vision Standard:**

Electrical

3.6 - 4.6 (12VDC External Power Supply)
4.0 - 4.9 (PoE) **Power Consumption (W):**

Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE, RJ45 with Screw Locks **Connector:**

Power over Ethernet (PoE) or via GPIO **Power Supply:**

2 digital input, 2 digital output **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, Free-Run, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

10-pin Samtec **GPIO Connector Type:**

2 opto-isolated inputs, 2 opto-isolated outputs **Ports:**

Threading & Mounting

Mount:

C-Mount

Mounting Threads:

1/4-20 with Tripod Mount Adapter [#34-966](#)

Environmental & Durability Factors

Operating Temperature (°C):

-20 to +60

Storage Temperature (°C):

-40 to +80

Regulatory Compliance

REACH 201:

[Compliant](#)

Certificate of Conformance:

[View](#)

Country of Origin:

Canada

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- TurboDrive™ Technology Achieve Frame Rate up to 800 fps
- Compact, Lightweight, Robust All Metal Body
- Global Electronic Shutter with Exposure Control and Advanced Feature Set



Teledyne
Authorized
Distributor

Teledyne DALSA Genie™ Nano GigE Cameras are available in a range of Sony Pregius and On Semiconductor CMOS sensors. These GigE PoE cameras provide high speed, low noise, and global electronic shutters. The proprietary TurboDrive™ technology allows the Genie™ Nano to exceed standard frame rates, delivering up to 800 fps while retaining full image quality. These cameras come with a host of advanced feature set such as multi ROI windows and Burst Acquisition, which utilizes onboard memory buffer to achieve even faster frame rates.* Teledyne DALSA Genie™ Nano GigE Cameras are packaged in compact and robust all metal housing, making them ideal for electronics inspection, industrial metrology, and Intelligent Traffic Systems (ITS) applications.

Note: Frame rates achievable through TurboDrive™ or Burst Acquisition could vary with factors such as image quality and resolution.

Sapera LT is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sapera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sapera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.