

LightPath 354115 | 9.2mm Dia., 0.54 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-692** CLEARANCE CONTACT US

[Other Coating Options](#)

-

1

+

₹3,823.65

ADD TO CART

Qty 1+

₹3,823.65

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
9.20 ±0.015

Effective Focal Length EFL (mm):
6.75 @633nm

Numerical Aperture NA:
0.54

Substrate: [D-ZK3](#)

Focal Length Tolerance (%) : ±1
Aspheric Design Wavelength (nm) : 633
Coating : BBAR (600-1050nm)
Coating Specification : R _{abs} <1.0% @ 600 - 1050nm
Surface Quality : 60-40
Clear Aperture CA (mm) : 7
Edge Thickness ET (mm) : 2.15
Center Thickness CT (mm) : 4.08 ±0.02
f/# : 0.93
Bevel : Protective bevel as needed
Compatible Window : Thickness: 0.25 (t) (mm) Material: BK7
Lightpath Lens Code : 354115
Operating Temperature (°C) : ≤200
Type : Aspheric Lens
Wavelength Range (nm) : 600 - 1050
Typical Applications : Collimate or Focus Laser Light
Working Distance (mm) : 4.3
Conjugate Distance : Infinite

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View