

Lightpath 7100331 | 5.3mm FL, f/1.3, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock **#15-686** **9 In Stock**

-

1

+

₹12,600

ADD TO CART

Volume Pricing	
Qty 1+	₹12,600 each
Need More?	Request Quote

Product Downloads

General	
Thickness: 0.70mm Material: Si	Compatible Window:
7100331	Lightpath Lens Code:

Physical & Mechanical Properties	
4.28	Clear Aperture CA (mm):
Matte Black Anodized Aluminum Housing	Construction:

Length (mm):		7.25
Front Diameter (mm):		12.00
Optical Properties		
Effective Focal Length EFL (mm):		5.30
Substrate: ☐		Black Diamond™ BD-6
f/#:		1.3
Coating:		BBAR (8000-12000nm)
Wavelength Range (nm):		8000 - 12000
Coating Specification:		R _{avg} <0.75% @ 8000 - 12,000nm
Index of Refraction (n _d) @ 10μm:		2.7816
Index of Refraction (n _d) @ 14μm:		2.7683
Index of Refraction (n _d) @ 4μm:		2.7978
Working Distance (mm):		7.30
Sensor		
Recommended Detector Format (H x V/Pixel Size):		320 x 240 / 12μm
Threading & Mounting		
Mounting Threads:		M12 x 0.5
Thread Length (mm):		3.75
Material Properties		
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):		22.5
Thermo-optic coefficient dn/dT:		30.5 x 10 ⁻⁶ @ 10μm
Regulatory Compliance		
RoHS 2015:		Compliant
Certificate of Conformance:		View
Reach 247:		Compliant
Country of Origin:		China
Imported By:		Edmund Optics India Private Limited

Product Details

- Precision Molded Chalcogenide Lenses
- Compact Designs for Thermal Imaging Cameras
- Focal Lengths from 2.7 to 24mm

Lightpath® Thermal Imaging Assemblies are a cost-effective alternative to diamond turned infrared lenses for applications in the mid-wave infrared (MMR) or long-wave infrared (LWR). These lenses are molded from BD6™, a chalcogenide glass that offers high transmission from 1 to 15μm and is also optically athermalized from -40 to +85°C. These lenses feature a broadband antireflection coating from 8 to 12μm and are mounted in compact black anodized aluminum housings that are threaded to allow for adjustable focus. Lightpath Thermal Imaging Assemblies are ideal for medical diagnostics, gas sensing, thermography, thermal imaging, security, and manufacturing process control applications. Lenses with focal lengths from 2.7 to 24mm are available, covering detector sizes from 80 x 80 to 640 x 480 pixels.