

Coherent® Beam Position Thermopile Power Sensors 1168340 | 10mW-10W

See More by [Coherent®](#)



Stock #68-628 10 TO 12 DAYS

- 1 + ₹160,080.00

ADD TO CART

Qty 1+
₹160,080.00

Volume Pricing
Request Quote

Get Product Downloads

Active Area Diameter (mm):
16

Model Number:
LM-10
Coherent Part Number: 1168340

Type:
Meterless

Type of Sensor:
Quad Element Thermopile

Length of Cable (m):

2.5
Linearity (%): ±1
Computer Interface: USB
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 10,600
Long Pulse Joule Mode Range (J): 0.5 - 10
Long Pulse Joule Mode Accuracy (%): ±3
Spectral Compensation Accuracy (%): ±1.5
Cooling Method: Air
Maximum Incident Beam Power (W): 10
Maximum Incident Power Density (kW/cm²): 6
Power Range: 10mW - 10W
Wavelength Range (µm): 0.25 - 10.6
Maximum Incident Energy Density: 600mJ/cm² (10ns, 1064nm)
Minimum Power (mW): 10

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View