

[See all 13 Products in Family](#)

M55 x 0.75 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #25-087 **2 In Stock**

MRP ₹6,709

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹6,709 each
Qty 10-25	₹6,406 each
Need More?	Request Quote

Product Downloads

General

Mounted Imaging Filter **Type:**

Physical & Mechanical Properties

50.50 **Clear Aperture CA (mm):**

57.60 **Diameter (mm):**

Dichroic **Construction:**

Optical Properties

Uncoated **Coating:**

Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm **Extinction Ratio:**

Float Glass **Substrate:**

95% Efficiency **Polarization:**

Single: 30
Crossed: 0.15 **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

Threading & Mounting

M55 x 0.75 **Filter Thread:**

6.80 **Mount Thickness (mm):**

Environmental & Durability Factors

-15 to +70 **Operating Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Japan **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

Technical Information

