

Low Profile Z-Axis Bracket for 32mm Metric Stages



32mm/1.25" Center drive stage and its X-Y-Z configuration



Stock **#56-359** **3 In Stock**

-

1

+

₹7,335

ADD TO CART

Volume Pricing	
Qty 1+	₹7,335 each
Need More?	Request Quote

Product Downloads

General

Type:

Adapter Brackets & Plates

Physical & Mechanical Properties

Travel (mm):

Center

Bracket Thru-Hole:

6.4mm

41.5 x 31.8 x 31.8	Dimensions (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Preloaded Ball Bearing Design for Low-Friction Linear Adjustment
 - Solid-Top and Thru-Hole Versions
 - English or Metric Micrometer Drive and Fine Screw Drive Available
 - Stackable for 2-Axis or 3-Axis Movement
- Metric Ball Bearing Translation Stages with a metric hole patterns on both the top and bottom plates feature a preloaded ball bearing design that provides straight line accuracy of 2µm per 25mm of travel. These stages are available in multiple stage sizes and configurations of drive mechanism, drive orientation, and travel distance, as well as the option of a clearance-thru hole. The Fine Screw (64 Pitch) models provide fine resolution positioning while the English and Metric micrometer models provide a position readout in 0.001inch or 0.01mm graduations. Metric Ball Bearing Translation Stages are designed to reduce friction, allowing smooth linear motion without backlash or sideplay. All stages include screws for creating an X-Y stage and a position lock.
- Note:** [Adapter Plates](#) and [Z-Axis Brackets](#) are available for breadboard mounting application and X-Y-Z configuration. Brackets include screws for assembling X-Y-Z stages from multiple stages.