

Micro Manual Rotary Stage



Stock #56-572 [CONTACT US](#)

- 1 + ₹32,861

ADD TO CART

Volume Pricing

Qty 1+	₹32,861 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Coarse Adjustment Tool Included **Note:**

Physical & Mechanical Properties

Rotary **Type of Movement:**

Slide-Fit **Guide System:**

Stage Size (mm):

25.4 Dia.

Travel (°):

17 (Fine), 360 (Coarse)

Center Hole:

0.275" (7.0mm) Thru with 5/16-24 TPI Thread

Construction:

Black Anodized Stage Body with Stainless Steel Thumb Screw

Load Capacity, Normal (kg):

0.23

Stage Size (inches):

1 Dia.

Weight (g):

10

Table Diameter (mm):

19.05 Dia.

Table Diameter (inches):

0.75 Dia.

Travel Per Knob Rotation (µrad):

36.7

Hardware & Interface Connectivity

Type of Drive:

Fine Screw (80 Pitch)

Threading & Mounting

Mounting Threads:

Top: (6) 0-80 on 0.375" (9.5 mm) B.C.

Bottom: (6) 0-80 on 0.428" (10.9 mm) B.C.

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Compliant](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited

Product Details

- Small Footprint
- 17 Degrees of Fine Adjustment
- 360 Degrees of Coarse Adjustment

At 10mm high and 20mm in diameter, this micro rotary stage is a dimensional breakthrough. 360 degree coarse adjustment is achieved by manually rotating the component platform. Coarse adjustment tool is included for ease of rotation in space restricted environments. An 80 TPI fine screw allows for 17 degrees of fine adjustment. This stage can be mounted to other components in your system via six 0-80 tapped holes in the bottom platform. Optical components can be mounted to the top platform via six 0-80 tapped holes or 5/16-24 tapped center hole.

Technical Information

Micro Manual Rotary Stage

