

[See all 39 Products in Family](#)

Model 1108P, 0.5mW Linear Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock #62-715 [CONTACT US](#)

- 1 + MRP ₹1,30,095

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,30,095 each
Need More?	Request Quote

Product Downloads



General

Warm-Up Time (minutes):
10

Manufacturer:
Lumentum

Type of Laser:
HeNe

Laser Class - CDRH:

1108P **Model Number:**

Physical & Mechanical Properties

N/A **Pointing Stability after Warm Up (mrad/°C):**

0.46 **Weight (lbs):**

7.00 **Length of Laser Head (inches):**

Static Alignment:
Centered to Outer Cylinder: $\pm 0.01''$
Parallel to Outer Cylinder: ± 1.0 mrad

N/A **Pointing Stability (mrad/°C):**

1.245 **Diameter of Laser Head (inches):**

Optical Properties

500:1 **Polarization:**

TEM₀₀ **Spatial Mode:**

632.80 **Wavelength (nm):**

± 3 **Beam Diameter Tolerance (%):**

± 3 **Beam Divergence Tolerance (%):**

Mean Power over 8 hrs: ± 2.5 **Maximum Drift:**

0.48 **Beam Diameter (mm):**

1.80 **Beam Divergence (mrad):**

Red **Color:**

>95% **Mode Purity (TEM₀₀):**

Electrical

0.5 **Output Power (mW):**

30 Hz - 10 MHz 0.1% **RMS Noise:**

1090 **Longitudinal Mode Spacing, Nominal (MHz):**

0.5 **Minimum Output Power, TEM₀₀ (mW):**

Hardware & Interface Connectivity

Power Supply:
[#11-379](#) (110/220V AC), [#11-382](#) (12VDC), [#11-383](#) (24VDC), [#11-386](#) (110/220V AC)

Free Space **Output Type:**

Environmental & Durability Factors

-40 to +70 **Operating Temperature (°C):**

0 to 100%, non-condensing **Operating Humidity:**

-40 to +150 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

